


KKT Filter Kit (shipped loosely with vented chiller)



NOTE: Bypass valve (2) should **always** be **CLOSED** for normal operation and opened only when servicing the filter

NOTE: Isolating valve (1) should **always** be **OPEN** for normal operation and closed only when servicing the filter

NOTE: Isolating valve (1) should **always** be **OPEN** for normal operation and closed only when servicing the filter

IMPORTANT: filter assembly to be installed indoors.
Temperature Range: + 40...+100 F

External inline Filter (max. 100micron)

GE filter cBoxX 60 / cBoxX 100 / 120			
Part#	supplier	Part	Qtys
H615-050-R	ILLCO	HEDLAND Mechanical Flowmeter: 1 1/2 in Connection Size, FNPT, Water, 5-50gpm	1
150236		Pentair 1-1/2" Big Blue 20" Filter Housing	1
5754T35	McMaster - Carr	Isolating ball valve 1-1/2"	3
SH144368		Pentair SW-4 Filter Wrench for 20" housing	1
144928		Pentair WB-PC Mounting Bracket Kit	1
151122		Pentair O-Ring for Big Blue and Heavy Duty Housings	1
355226-43		Pentair 20" Big Blue String Wound Filter-100micron	1
9702040	ILLCO	Water Pressure Gauge, 2-1/2" Btm Mnt 0-100psi	2
		Dial Size: 2-1/2"	
		Connection Size: 1/4"	
		Connection Ends: MPT	
		Connection Location: Bottom	
Range: 0 - 100 psi or 0 - 700 kPa			

<p>KKT chillers, Inc. 765 Dillon Drive Wood Dale, IL 60191 Phone: +1 (847) 734 1600 Fax: +1 (847) 734 1601</p>	KKT chillers, Inc			
	cBoxX - KKT Filter Kit (for vented chillers only)			
Created: John Carmody	SIZE	Fax No:	Drawing No:	REV. A
Date: 12.28.23	SCALE	Page		1 of 1

8

7

6

5

4

3

2

1